

**metabo****Angle grinder Stainless steel, Type: WEV17-125****Order data**

Order number	077133 WEV17-125
GTIN	4061792176225
Item class	03D

**Description****Version:****You define the limit – not your machine.**

With devices from 850 to 1,900 watts, you will find the right angle grinder for every requirement and every application. Extremely robust angle grinder with high gear reduction and **highly reduced**, adjustable **speed** for cool grinding. Perfect **for use on stainless steel**.

- **Metabo S-automatic mechanical safety shut-off: Minimizes kick-back when the disc is blocked.**
- **Electronic overload protection, soft start and restart protection.**
- **Gear housing can be mounted in 90° increments for left-handed operation or for cutting.**
- **Constant speed under load.**
- **Longer service life, more power: The Metabo Marathon motor with patented dust protection, up to 20% more overload capacity and 50% more torque.**
- **Tool-free, fast disc change at the touch of a button with the Metabo M-Quick system.**
- **Protective hood that can be adjusted without tools; can be fixed in a torsion-proof manner.**
- **Low-vibration additional handle Metabo VibraTech (MVT).**
- **Switch-off carbon brushes to protect the motor.**

**Supplied with:**

Supplied with torsion-resistant protective hood, clamping set, additional handle and two-pin wrench.

**Technical description**

Dead man's circuit	yes
--------------------	-----

Weight	2.5 kg
Soft start	yes
Power consumption	1700 W
Restart block	yes
Connection thread	M14
Manufacturer's designation	WEV 17-125 Quick Inox
maximum disc Ø	125 mm
Cable type	4
Special features	Quick-change system
Power supply	Mains-powered
No load speed	2000 - 7600 min <sup>-1</sup>
Type of product	Angle grinder