

metabo**Angle grinder, Type: WEPBA24230****Order data**

Order number	077150 WEPBA24230
GTIN	4007430337641
Item class	03D

Description**Version:**

Strong 230-mm angle grinder with Metabo Marathon motor with patented dust protection to ensure a long service life:

- **Electronic safety shut-off function: reduces kick-back when the disc is blocked, providing excellent protection for the operator.**
- **Electronic overload protection and restart inhibit.**

Supplied with:

Supplied with protective hood, additional handle, quick-clamping nut.

Power consumption: 2400 W

No load speed: 6600 min⁻¹

Torque: 17 N·m

Connection thread: M14

maximum disc Ø: 230 mm

Weight: 6.2 kg

Technical description

Cable length	4 m
Kick-back stop	yes
Soft start	yes
Dead man's circuit	yes
Weight	6.2 kg

maximum disc Ø	230 mm
Mains frequency	50 Hz
Power consumption	2400 W
Restart block	yes
Torque	17 N·m
Connection thread	M14
Power supply	Mains-powered
No load speed	6600 min ⁻¹
Nominal voltage	240 V
Type of product	Angle grinder