

metabo
Angle grinder, Type: WE26-230

Order data

Order number	077150 WE26-230
GTIN	4007430268334
Item class	03D

Description
Version:

Strong 230-mm angle grinder with Metabo Marathon motor with patented dust protection to ensure a long service life:

- **Electronic safety shut-off function: reduces kick-back when the disc is blocked, providing excellent protection for the operator.**
- **Electronic overload protection and restart inhibit.**

Supplied with:

Supplied with protective hood, additional handle, quick-clamping nut.

Technical description

maximum disc Ø	230 mm
Restart block	yes
maximum vibration to EN	6.4 m/s ²
maximum speed	6600 min ⁻¹
Soft start	yes
Weight	6.3 kg
Power consumption	2600 W
maximum cutting depth	65 mm
Manufacturer's designation	WE 26-230 MVT Quick

Power supply	Mains-powered
Special features	Soft start
Special features	Restart inhibit
Type of product	Angle grinder