

**metabo****Angle grinder Flat head, Type: WEF15-125****Order data**

Order number	077136 WEF15-125
GTIN	4007430275707
Item class	03D

**Description****Version:****You define the limit – not your machine.**

With devices from 850 to 1,900 watts, you will find the right angle grinder for every requirement and every application. Powerful **flat head** angle grinder for fast working at sharp angles up to 43° and hard-to-reach areas.

- **Designed to remove welding slag, rust or paint in tight frame designs and for work in strained positions.**
- **Metabo S-automatic mechanical safety shut-off: Minimizes kick-back when the disc is blocked.**
- **Electronic overload protection, soft start and restart protection.**
- **Gear housing can be mounted in 90° increments for left-handed operation or for cutting.**
- **Constant speed under load.**
- **Longer service life, more power: The Metabo Marathon motor with patented dust protection, up to 20% more overload capacity and 50% more torque.**
- **Metabo Quick for tool-free disc change using quick clamping nut.**
- **Protective hood that can be adjusted without tools; can be fixed in a torsion-proof manner.**
- **Additional handle Metabo VibraTech (MVT) for vibration damping to protect the user's health.**
- **Switch-off carbon brushes to protect the motor.**

**Supplied with:**

Supplied with torsion-resistant protective hood, clamping set, additional handle and two-pin wrench.

## Technical description

Kick-back stop	yes
Power supply	Mains-powered
maximum disc Ø	125 mm
Soft start	yes
Connection thread	M14
Cable length	4 m
Power consumption	1550 W
Restart block	yes
Weight	2.7 kg
Manufacturer's designation	WEF 15-125 Quick
Special features	Quick-change system
No load speed	11000 min <sup>-1</sup>
Type of product	Angle grinder