

**metabo****Angle grinder, Type: WEA19-1800****Order data**

Order number	077148 WEA19-1800
GTIN	4007430314307
Item class	03D

**Description****Version:**

**Powerful 180 mm angle grinder with the cutting depth of a 230 mm angle grinder.**

- **Reduced vibrations minimise fatigue when working thanks to Metabo VibraTech (MVT) additional handle and integrated autobalancer.**
- **Electronic soft start and restart protection.**
- **Gear housing can be mounted rotated in steps of 90°.**
- **Perfect ergonomics thanks to slim grip area for maximum control and easy overhead work.**
- **Metabo Marathon motor with new cooling and carbon brush system for double the service life.**
- **Tacho-Constamatic (TC) full-wave electronics: High work progress due to constant speed under load.**
- **M-Quick system for tool-free disc changes at the touch of a button.**
- **Protective hood that can be adjusted without tools; can be fixed in a torsion-proof manner.**
- **Metabo S-automatic mechanical safety shut-off: Minimizes kick-back when the disc is blocked to the lowest level on the market – for maximum user protection and to ensure work can continue quickly.**
- **Electronic soft start and restart protection.**
- **Switch-off carbon brushes to protect the motor.**

**Supplied with:**

Supplied with protective hood, additional handle, M-Quick clamping nut.

**Technical description**

Special features	Large cutting depth
Special features	M-Quick System
Power consumption	1900 W
maximum vibration to EN	4.9 m/s <sup>2</sup>
maximum speed	8200 min <sup>-1</sup>
Manufacturer's designation	WEA 19-180 Quick RT
Restart block	yes
Cable length	4 m
maximum cutting depth	60 mm
Weight	2.7 kg
maximum disc Ø	180 mm
Power supply	Mains-powered
Type of product	Angle grinder