

metabo**Cordless hammer drill with Li-ion battery, Type: SB18LBL****Order data**

Order number	070121 SB18LBL
GTIN	4007430337597
Item class	03D

Description**Version:****Cordless hammer drill with brushless motor and two-speed gearbox.**

Choose between a complete set of 2 battery packs, charger and sturdy plastic case or the machine without accessories in a box if you already have a few batteries. Of course, you can also buy battery packs and chargers separately.

By the way, all Metabo battery packs come with a 3-year warranty, irrespective of the number of charging cycles.

Further details such as the bright LED work light and the handy belt hook ensure even more comfort when working. For the most demanding applications, we recommend brushless types, which you can recognise immediately by the "BL" in the designation. They also have thermal overload protection that protects the motor from overheating.

- **Cordless impact drill screwdriver with extremely compact design for general applications.**
- **Impact drilling function for drilling in masonry.**
- **Integral LED work light with backlight function for optimum brightness in the working area.**
- **With handy belt hook and bit deposit, can be fixed either on the right or left.**

Advantage:

Batteries are 100% compatible – now also across different manufacturers.

All 18 V devices and battery packs from CAS partners are 100% compatible with each other. CAS stands for "Cordless Alliance System".

Supplied with:

Supplied with quick-clamping drill chuck, 2× Li-ion batteries, charger and metaBox.

Note:

See No. 073870 – 073890 for suitable batteries and chargers.

Technical description

Packaging	Metabox
typical application	Medium
suitable battery - supplier / battery type / voltage	Type CAS 18 V
maximum hammer rate	26000 min ⁻¹
maximum twist drill size Ø in wood	32 mm
Manufacturer's designation	SB 18 L BL
maximum torque soft	25 Nm
maximum twist drill size Ø in steel	13 mm
Battery voltage	18 V
Quick-clamping chuck range	1.5 mm
Power supply	Mains operated
Type of rechargeable battery	Lithium-ion
No load speed	0 - 550
No load speed	0 - 1850
Weight including rechargeable battery	1.4 kg
maximum torque hard	60 Nm
Number of rechargeable batteries contained	2
Weight without battery	0.9 kg
Battery capacity	2 Ah
maximum twist drill size Ø in concrete	10 mm
Motor design	brushless
Type of product	Impact drill /screwdriver

