

metabo
Cordless drill / driver without rechargeable battery, Type: BSLTBL


Order data

Order number	070261 BSLTBL
GTIN	4007430302199
Item class	03D

Description

Version:

Cordless drill drivers with and without Metabo Quick System.

The **Quick System saves a lot of time** when switching frequently between drilling and screwdriving. The drill chuck with drill is exchanged for bit holders and bits within a matter of seconds, without any tools.

Choose between a **complete set** of 2 battery packs, charger and a robust plastic case or the **machine without accessories** in a box if you already have some batteries. Of course, you can also purchase battery packs and chargers separately. By the way, all Metabo battery packs are covered by a **3-year warranty**, regardless of the number of charging cycles.

Additional details such as the bright **LED work light** and the practical **belt hook** provide even more comfort when working.

- **Brushless drill/driver with optimal performance for demanding applications.**
- **Unique Metabo brushless motor for fast work progress and maximum efficiency in drilling and screwdriving.**
- **Integrated work light for illuminating the working area.**
- **With practical belt hook and bit holder, optionally fixable on the right or left.**
- **LiHD battery pack for ultimate performance, ultra-long life and durability.**

For the most demanding applications, we recommend brushless types, which you can recognise immediately by the "BL" in the designation. They also have thermal overload protection that protects the motor from overheating.

Advantage:

Batteries are 100% compatible – now also across different manufacturers.

All 18 V devices and battery packs from CAS partners are 100% compatible with each other. CAS stands for “Cordless Alliance System”.

Supplied with:

With quick-clamping drill chuck, without battery, without charger.

Note:

See No. 073870 – 073890 for suitable batteries and chargers.

Technical description

Weight without battery	1.2 kg
suitable battery - supplier / battery type / voltage	Type CAS 18 V
Quick-clamping chuck range	1.5 - 13 mm
Number of rechargeable batteries contained	0
maximum twist drill size Ø in steel	13 mm
typical application	Strong
Battery voltage	18 V
No load speed	0 - 600 min ⁻¹
No load speed	0 - 2100 min ⁻¹
maximum twist drill size Ø in wood	38 mm
maximum torque hard	75 Nm
Weight including rechargeable battery	1.6 kg
maximum torque soft	34 Nm
Packaging	Metabox
Motor design	brushless
Manufacturer's designation	BS 18 LT BL
Power supply	Mains operated
Type of rechargeable battery	Lithium-ion
Type of product	Drill/drivers
USP1	18V
USP2	Brushless motor, without rechargeable battery, quick-change chuck clamping range 1.5-13

Accessories

Battery packLi-Power Battery capacity 5,2 A·h	073870 5,2
Battery packLi-Power Battery capacity 2 A·h	073870 2
Battery packLi-Power Battery capacity 4 A·h	073870 4
Battery charger Type ASC55	073890 ASC55