

metabo**Cordless drill/driver with LiHD rechargeable battery, Type: BSLTBL****Order data**

Order number	070259 BSLTBL
GTIN	4007430334732
Item class	03D

Description**Version:****Cordless drill/driver with and without Metabo Quick system.**

The **Quick system saves a lot of time** if you frequently need to change between drilling and screwing. In just a few seconds, the drill chuck with drill can be replaced with a bit holder and a bit, without the need for any tools.

Choose between a **complete set** with 2 battery packs, charger and sturdy plastic case, or the **machine without accessories** in the box if you already have a few batteries. Of course, you can also buy battery packs and chargers separately. All battery packs from Metabo come with a **3-year warranty**, irrespective of the number of charge cycles.

Further highlights such as the bright **LED work light** and the handy **belt hook** ensure even greater convenience when working.

- **Brushless drill/driver with optimal performance for demanding applications.**
- **Unique Metabo brushless motor for fast work progress and maximum efficiency in drilling and screwdriving.**
- **Integrated work light for illuminating the working area.**
- **With practical belt hook and bit holder, optionally fixable on the right or left.**
- **LiHD battery pack for ultimate performance, ultra-long life and durability.**

For the most demanding applications, we recommend brushless types, which you can recognise immediately by the "BL" in the designation. They also have thermal overload protection that protects the motor from overheating.

Advantage:

Batteries are 100% compatible – now also across different manufacturers.

All 18 V devices and battery packs from CAS partners are 100% compatible with each other. CAS stands for “Cordless Alliance System”.

Supplied with:

Supplied with quick-change chuck, 2 pcs. LiHD rechargeable battery, chargers and metaBOX.

Note:

See No. 073870 – 073890 for suitable batteries and chargers.

Technical description

Power supply	Mains operated
Weight without battery	1.2 kg
suitable battery - supplier / battery type / voltage	Type CAS 18 V
maximum twist drill size Ø in steel	13 mm
No load speed	0 - 600 min ⁻¹
No load speed	0 - 2100 min ⁻¹
maximum torque soft	34 Nm
Motor design	brushless
Manufacturer's designation	BS 18 LT BL
typical application	Strong
Weight including rechargeable battery	1.8 kg
Quick-clamping chuck range	1.5 - 13 mm
Type of rechargeable battery	Lithium-ion
Battery voltage	18 V
maximum torque hard	75 Nm
Packaging	Metabox
Battery capacity	4 Ah
Number of rechargeable batteries contained	2
maximum twist drill size Ø in wood	38 mm
Type of product	Drill/drivers
USP1	18V

USP2

Brushless motor, with 2 rechargeable batteries, quick-change chuck clamping range 1.5-13

Accessories

Battery charger Type ASC55-8	073890 ASC55-8
Battery packLi-Power Battery capacity 2 A·h	073870 2
Battery packLi-Power Battery capacity 4 A·h	073870 4
Battery packLi-Power Battery capacity 5,2 A·h	073870 5,2
Battery charger Type ASC55	073890 ASC55