



Torque screwdriver without scale, to take interchangeable blades, maximum torque: 1600cNm



Order data

Order number	659958 1600
GTIN	7610733291755
Item class	63D

Description

Version:

Power grip with non-allergenic elastomer coating allows transmission of the required torque with no problems even with **wet or oily hands**. On reaching the set torque value, the screwdriver can be felt and heard to trigger and is then again immediately ready for use. The release torque is higher than the tightening torque (overload protection).

The desired torque can be set by stepless adjustment using a torque analyser (No. 654300 – 654460) and a 5 AF hexagon screwdriver (not supplied). To **take 8 mm interchangeable blades** (No. 659870 – 659884). With pistol grip for delivering high torques.

Standard:

Geprüft nach DIN EN ISO 6789.

Note:

The guaranteed measuring accuracy of the torque is achieved only once the torque range has been calibrated to DIN EN ISO 6789.

Technical description

Direction of tightening	Right-hand tightening
-------------------------	-----------------------

Measurement technology	mechanical
Setting the trigger value	without setting scale (requires torque analyser)
Feedback	triggering
Overall length L	126 mm
suitable interchangeable blades	8 mm
Connection format	exchangeable blade
Data can be recorded	no
set torque	1000 cNm
Torque measuring accuracy	±6 %
maximum torque	1600 cNm
Trigger principle	mechanical short travel release
Test certificate	Manufacturer's test certificate
Reversible reading	cNm
Standard	DIN EN ISO 6789
Torque range	3.2 - 16 Nm
Torque range	320 - 1600 cNm
Measurement process	Torque
Calibration	O6
Calibration	O7
Release signalling	acoustic
Release signalling	haptisk
set torque	10 Nm
Adjustable trigger value	preset
Torque fixed setting	no
Type of product	Torque screwdriver

Services

Calibration and adjustment Torque screwdriver without scale maximum torque 0,04-20 N·m

020170 0,04-20

