

Garant
GARANT Master UNI solid carbide torus cutter, TiSiN, Ø DC / R1: 10/1,5mm


Order data

Order number	206367 10/1,5
GTIN	4067263047001
Item class	11Z

Description

Version:

For **roughing and finishing at very high feed rates** with smooth cutting action. **Newly developed geometry and high-performance coating** for outstanding production results and very long tool life with a variety of materials. Unequal spacing gives **high intrinsic stability** and smooth cutting action. Tolerance: corner radius $R_1 = \pm 0.005 \text{ mm}$.

Dimensions similar to **DIN 6527**.

Advantage:

- **Particularly low vibration running.**
- **Special flute profile, large flutes.**
- **Specially matched edge honing.**
- **Optimised substrate for hardness and toughness.**

Technical description

Shank Ø D_s	10 mm
Recess Ø D_1	9.7 mm
Corner radius R_1	1.5 mm
No. of teeth Z	4
Flute length L_c	22 mm
Feed f_z for copy milling in steel $< 900 \text{ N/mm}^2$	0.09 mm
Overall length L	72 mm
Shank	DIN 6535 HB to h6

Overhang length L_1 incl. recess	32 mm
Cutting edge $\varnothing D_c$	10 mm
Feed f_z for side milling in steel $< 900 \text{ N/mm}^2$	0.08 mm
Feed f_z for copy milling in stainless steel $> 900 \text{ N/mm}^2$	0.058 mm
Feed f_z for side milling in INOX $> 900 \text{ N/mm}^2$	0.05 mm
Helix angle	42 degrees
Series	Master Uni
Coating	TiSiN
Tool material	Solid carbide
Standard	Works standard
Type	N
Tolerance nominal \varnothing	e8
Helix angle characteristic	unequal spacing
Spacing of the cutters	unequal spacing
Direction of infeed	horizontal, oblique and vertical
Cutting width a_e for milling operation	$0.3 \times D$ for side milling
Cutting width a_e for milling operation	$0.3 \times D$ for side milling
Cutting width a_e for milling operation	$0.05 \times D$ for copy milling
Through-coolant	no
Machining strategy	HPC
Type of product	Torus cutter

User data

	Suitability	V_c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	280 m/min	N
Steel $< 500 \text{ N/mm}^2$	suitable	260 m/min	P
Steel $< 750 \text{ N/mm}^2$	suitable	240 m/min	P
Steel $< 900 \text{ N/mm}^2$	suitable	190 m/min	P

Steel < 1100 N/mm ²	suitable	180 m/min	P
Steel < 1400 N/mm ²	suitable	150 m/min	P
INOX < 900 N/mm ²	suitable	90 m/min	M
INOX > 900 N/mm ²	suitable	80 m/min	M
Ti > 850 N/mm ²	suitable	40 m/min	S
GG(G)	suitable only under restricted conditions	250 m/min	K
Uni	suitable		
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		
dry	suitable		
Air	suitable		