



Torque screwdriver with scale, to take interchangeable blades, maximum torque: 200cNm



Order data

Order number	659957 200
GTIN	7610733291700
Item class	63D

Description

Version:

Power grip with non-allergenic elastomer coating allows transmission of the required torque with no problems even with **wet or oily hands**. On reaching the set torque value, the screwdriver can be felt and heard to trigger and is then again immediately ready for use. The release torque is higher than the tightening torque (overload protection).

The desired torque is set using an adjustment wheel at the end of the handle. Putting the wheel into the locked position prevents inadvertent changes to the setting. Easy to read micrometer scale, protected against dirt. To **take 6 mm interchangeable blades** (No. 659920 – 659928).

Standard:

Geprüft nach DIN EN ISO 6789.

Note:

The guaranteed measuring accuracy of the torque is achieved only once the torque range has been calibrated to DIN EN ISO 6789.

Technical description

Measurement technology	mechanical
Adjustable trigger value	adjustable
Torque measuring accuracy	±6 %
Connection format	exchangeable blade
Test certificate	Manufacturer's test certificate
Measurement process	Torque

Calibration	O1
Standard	DIN EN ISO 6789
maximum torque	200 cNm
Trigger principle	mechanical short travel release
Torque range	0.4 - 2 Nm
Release signalling	acoustic
Release signalling	haptisk
Scale graduation, 1 graduation =	5 cNm
Setting the trigger value	with adjustment scale
Data can be recorded	no
Overall length L	124 mm
Direction of tightening	Right-hand tightening
Torque range	40 - 200 cNm
Feedback	triggering
Display	analogue
suitable interchangeable blades	6 mm
Torque fixed setting	no
Type of product	Torque screwdriver

Services

CalibrationTorque screwdriver maximum torque 0,04-20 N·m	020200 0,04-20
--	----------------