

Garant**ESD Eurobox trolley, Type: TE37****Order data**

| | |
|--------------|---------------|
| Order number | 971970 TE37 |
| GTIN | 4067263515623 |
| Item class | 9GD |

Description**Version:**

ESD conductive Eurobox trolley in stable steel construction. Platforms made of folded sheet metal, adjustable at 280 mm intervals. Platforms can be secured in different positions and at inclinations of 15° and 30° for easier access to the bins. The bottom platform is fixed to the frame and cannot be inclined. ESD-conductive Haptoprene® handle with impact-resistant polypropylene. **Electrically conductive wheels:** 2 fixed wheels and 2 castors (with brakes) with treadless TPE tyres, roller bearings, with fibre shields.

Application:

Suitable for use in EPAs with a conductive floor covering. The grounding is provided via the wheels; a separate grounding connection is not necessary. All plastic parts are conductive to prevent surface charging.

Standard:

DIN EN 61340-5-1

Colour:

Similar to RAL 7035 light grey **ESD powder-coated.**

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.
For suitable Euroboxes see No. 972350.

Technical description

| | |
|--|--------------------------|
| Height | 1735 mm |
| Depth | 670 mm |
| Wheel Ø | 125 mm |
| Load capacity per platform | 50 kg |
| maximum load capacity | 250 kg |
| Platform area depth | 610 mm |
| Number of fixed wheels without parking brake | 2 |
| Width | 1300 mm |
| Weight | 85 kg |
| Inclination adjustable | 15 degrees |
| Inclination adjustable | 30 degrees |
| Material of wheels | TPE |
| Platform area width | 1240 mm |
| electrostatic characteristic | EGB/ESD |
| Number of castors with parking brake | 2 |
| Height adjustment interval | 280 mm |
| Type of product | Materials supply trolley |