



## Torque screwdriver with scale, to take interchangeable blades, maximum torque: 500cNm



### Order data

Order number	659957 500
GTIN	7610733291717
Item class	63D

### Description

#### Version:

**Power grip** with non-allergenic elastomer coating allows transmission of the required torque with no problems even with **wet or oily hands**. On reaching the set torque value, the screwdriver can be felt and heard to trigger and is then again immediately ready for use. The release torque is higher than the tightening torque (overload protection).

The desired torque is set using an adjustment wheel at the end of the handle. Putting the wheel into the locked position prevents inadvertent changes to the setting. Easy to read micrometer scale, protected against dirt. To **take 6 mm interchangeable blades** (No. 659920 – 659928).

#### Standard:

Geprüft nach DIN EN ISO 6789.

#### Note:

The guaranteed measuring accuracy of the torque is achieved only once the torque range has been calibrated to DIN EN ISO 6789.

### Technical description

Torque range	1 - 5 Nm
Scale graduation, 1 graduation =	10 cNm
Setting the trigger value	with adjustment scale
Connection format	exchangeable blade
Standard	DIN EN ISO 6789
Measurement process	Torque

Display	analogue
maximum torque	500 cNm
Torque range	100 - 500 cNm
Adjustable trigger value	adjustable
Data can be recorded	no
Trigger principle	mechanical short travel release
Measurement technology	mechanical
Calibration	O1
Release signalling	acoustic
Release signalling	haptisk
Feedback	triggering
Test certificate	Manufacturer's test certificate
Direction of tightening	Right-hand tightening
Torque measuring accuracy	±6 %
Overall length L	124 mm
suitable interchangeable blades	6 mm
Torque fixed setting	no
Type of product	Torque screwdriver

## Services

CalibrationTorque screwdriver maximum torque 0,04-20 N·m	020200 0,04-20
--	----------------