



Torque screwdriver without scale, to take interchangeable blades, maximum torque: 500cNm



Order data

Order number	659958 500
GTIN	7610733291748
Item class	63D

Description

Version:

Power grip with non-allergenic elastomer coating allows transmission of the required torque with no problems even with **wet or oily hands**. On reaching the set torque value, the screwdriver can be felt and heard to trigger and is then again immediately ready for use. The release torque is higher than the tightening torque (overload protection).

The desired torque can be set by stepless adjustment using a torque analyser (No. 654300 – 654460) and a 5 AF hexagon screwdriver (not supplied). To **take 6 mm interchangeable blades** (No. 659920 – 659928).

Standard:

Geprüft nach DIN EN ISO 6789.

Note:

The guaranteed measuring accuracy of the torque is achieved only once the torque range has been calibrated to DIN EN ISO 6789.

Technical description

Torque range	100 - 500 cNm
Direction of tightening	Right-hand tightening
Reversible reading	cNm
Test certificate	Manufacturer's test certificate
Measurement technology	mechanical
Measurement process	Torque

Setting the trigger value	without setting scale (requires torque analyser)
Feedback	triggering
Torque range	1 - 5 Nm
Connection format	exchangeable blade
maximum torque	500 cNm
Calibration	O6
Calibration	O7
Overall length L	124 mm
Standard	DIN EN ISO 6789
Release signalling	acoustic
Release signalling	haptisk
set torque	3 Nm
set torque	300 cNm
Adjustable trigger value	preset
suitable interchangeable blades	6 mm
Data can be recorded	no
Trigger principle	mechanical short travel release
Torque measuring accuracy	$\pm 6\%$
Torque fixed setting	no
Type of product	Torque screwdriver

Services

Calibration and adjustment Torque screwdriver without scale maximum torque 0,04-20 N·m

020170 0,04-20