



Torque screwdriver with scale, to take D 6.3 bits, maximum torque: 500cNm



Order data

Order number	659956 500
GTIN	7610733291694
Item class	63D

Description

Version:

Power grip with non-allergenic elastomer coating allows transmission of the required torque with no problems even with **wet or oily hands**. On reaching the set torque value, the screwdriver can be felt and heard to trigger and is then again immediately ready for use. The release torque is higher than the tightening torque (overload protection).

Bit holder with magnet to take C 6.3 bits.

The desired torque is set using an adjustment wheel at the end of the handle. Putting the wheel into the locked position prevents inadvertent changes to the setting. Easy to read micrometer scale, protected against dirt.

Standard:

Geprüft nach DIN EN ISO 6789.

Note:

The guaranteed measuring accuracy of the torque is achieved only once the torque range has been calibrated to DIN EN ISO 6789.

Technical description

Test certificate	Manufacturer's test certificate
Torque range	1 - 5 Nm
Weight	119 g
Measurement technology	mechanical
Bit socket	D 6.3
Data can be recorded	no
Calibration	O1

Torque range	100 - 500 cNm
Adjustable trigger value	adjustable
Release signalling	acoustic
Release signalling	haptisk
Trigger principle	mechanical short travel release
Setting the trigger value	with adjustment scale
Direction of tightening	Right-hand tightening
Connection format	Bit holder 1/4 inch
Feedback	triggering
Display	analogue
Scale graduation, 1 graduation =	10 cNm
Torque measuring accuracy	±6 %
Measurement process	Torque
Overall length L	144 mm
maximum torque	500 cNm
Standard	DIN EN ISO 6789
Torque fixed setting	no
Type of product	Torque screwdriver

Services

CalibrationTorque screwdriver maximum torque 0,04-20 N·m	020200 0,04-20
--	----------------