

**Garant****GARANT Softcut® HSI wide pitch, with bore, Ø D / number of teeth Z: 80/7mm**

## Order data

Order number	214906 80/7
GTIN	4045197674487
Item class	210

## Description

### Version:

Wear-resistant heat-treated steel with corrosion-inhibiting coating. Precise indexable insert seating by use of appropriate torque. Wide and close tooth pitches for individual milling strategies.

### Application:

Particularly suitable for machines with lower drive power and for machining at greater depths and small entry diameters.

### Note:

To use all **4 cutting edges**, the insert must **always be turned in the direction shown (anticlockwise)**.

Use GARANT torque screwdriver TQ No. **211750 size 2.2** with bit No. **674252 size 8IP**.

**For exact 90° corners, select  $a_p = 6$  mm.**

## Technical description

Mounting bore Ø	27 mm
maximum cutting depth $a_{p\max}$	6 mm

suitable indexable insert	SO.. 0836..
Pack of insert screws	219863 (8IP; 2.2 Nm)
Overall length $L_{tot}$	50 mm
Cutting edge $\varnothing D_c$	80 mm
Number of cutting edges Z	7
Series	Softcut®
Shank type	with bore
Setting angle $\kappa$	90 degrees
Milling application	Corner milling
Spacing of the cutters	unequal spacing
Through-coolant	yes
Tool exchange	PowerCard
Type of product	End / face mill

## Accessories

PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 8IP	674252 8IP
Set of insert screws 10 pieces	219863
Torque screwdriver, fixed setting set torque 2,2 N·m	211750 2,2