


**HOLEX Pro UNI solid carbide torus cutter, TiSiN, Ø DC / R1: 6/2,0mm**

**Order data**

Order number	206368 6/2,0
GTIN	4067263047162
Item class	12Y

**Description**
**Version:**

For **roughing and finishing at very high feed rates** with smooth cutting action. **Newly developed geometry and high-performance coating** for outstanding production results and very long tool life with a variety of materials. Unequal spacing gives **high intrinsic stability** and smooth cutting action. Tolerance: corner radius  $R_1 = \pm 0.005 \text{ mm}$ .

Dimensions similar to **DIN 6527**.

**Technical description**

Feed $f_z$ for copy milling in stainless steel $> 900 \text{ N/mm}^2$	0.04 mm
Cutting edge $\varnothing D_c$	16 mm
Helix angle	42 degrees
Overhang length $L_1$ incl. recess	19 mm
Feed $f_z$ for copy milling in steel $< 900 \text{ N/mm}^2$	0.058 mm
Feed $f_z$ for side milling in steel $< 900 \text{ N/mm}^2$	0.05 mm
Corner radius $R_1$	2 mm
Overall length L	57 mm
Shank $\varnothing D_s$	6 mm
No. of teeth Z	4
Flute length $L_c$	13 mm

Shank	DIN 6535 HB to h6
Recess $\varnothing D_1$	5.8 mm
Feed $f_z$ for side milling in INOX > 900 N/mm <sup>2</sup>	0.035 mm
Series	Pro Uni
Coating	TiSiN
Tool material	Solid carbide
Standard	Works standard
Type	N
Tolerance nominal $\varnothing$	e8
Helix angle characteristic	unequal spacing
Spacing of the cutters	unequal spacing
Direction of infeed	horizontal, oblique and vertical
Cutting width $a_e$ for milling operation	0.3×D for side milling
Cutting width $a_e$ for milling operation	0.3×D for side milling
Cutting width $a_e$ for milling operation	0.05×D for copy milling
Through-coolant	no
Machining strategy	HPC
Type of product	Torus cutter

## User data

	Suitability	$V_c$	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	250 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	240 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	220 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	180 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	170 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable	140 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable	90 m/min	M

INOX > 900 N/mm <sup>2</sup>	suitable	80 m/min	M
Ti > 850 N/mm <sup>2</sup>	suitable	35 m/min	S
GG(G)	suitable only under restricted conditions	240 m/min	K
Uni	suitable		
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		
dry	suitable		
Air	suitable		