




90° indexable milling cutter MECH17, with bore, Ø D / Zeff: 50/4Lmm



Order data

Order number	227655 50/4L
GTIN	4960664526420
Item class	250

Description

Version:

Notched indexable inserts reduce the cutting forces and vibration. Comparatively larger cutting widths a_e can be achieved with the same cutting depth a_p .

Technical description

Insert screw	229709 (T15; 3.5 Nm)
Number of effective inserts Z_{eff}	4
Cutting edge Ø D_c	50 mm
ISO code indexable insert	BDMT 170408
Overall length L_{tot}	78 mm
maximum cutting depth $a_{p \text{ max}}$	59 mm
suitable indexable insert	BD.. 1704
Mounting bore Ø	22 mm
Number of indexable inserts	16
Shank type	with bore

Setting angle κ	90 degrees
Milling application	End milling
Through-coolant	no
Type of product	End / face mill

Accessories

Clamping screw	229709
----------------	--------