

**Garant**

**Electrically height-adjustable workstation (2 lift columns) Load capacity max. 500 kg, Type: 1500**

**Order data**

Order number	920312 1500
GTIN	4067263736202
Item class	91S

**Description****Version:**

Base frame with anodised aluminium lift unit. With cross bracing for stabilisation. 50 mm thick worktop made of beech marine ply. Stepless height adjustment from 740 – 1140 mm, quickly and easily selected using the control panel. Control panel with memory function for 3 different working heights.

**Supplied with:**

4 floor levelling screws.

**Colour:**

Base frame with aluminium lift unit and steel hollow section RAL 7016 anthracite **powder-coated**.

**Recommendation:**

Ergonomic working for seated and standing tasks!

**Note:**

Only cabinet bodies up to maximum 500 mm height can be installed under the worktop.

**Technical description**

Material of worktop	Beech marine ply
Depth	750 mm

Stepless height adjustment	yes
Plug type, input	F
Worktop thickness	50 mm
Principle of height adjustment	complete structure
Height adjustment range (worktop surface) from – to	740 - 1140 mm
Worktop depth	750 mm
Power supply	Mains operated
maximum load capacity	500 kg
Supply voltage	250 V
Width	1500 mm
Worktop length	1500 mm
Surface worktop	clear varnished
Continuous load capacity	350 kg
Weight	75 kg
Workbench/desk load capacity - maximum distributed load (on wood)	500 kg
Type of height adjustment	electric
Insert thickness	50 mm
Height adjustment	25 mm
Type of product	Workbench