

KERN**Platform scales, type DS high resolution, maximum weighing range: 16kg**

Order data

Order number	479611 16
GTIN	4045761357044
Item class	47D

Description

Version:

- **Robust platform scales can be used as parcel, industrial, and counting scales.**
- **Display unit with numeral height 21 mm can be remote from platform; can be stood or mounted using flexible cable.**
- **Robust platform with a protective hood over the display unit.**
- **Simple, self-explanatory user guidance with (yes/no) dialogue in the display.**
- **Selectable mains or battery operation (battery available on request).**
- **Units of weight (e. g. screw weight) can be freely programmed.**
- **With automatic reference optimisation for exact counting.**
- **Adjustment programme CAL: For accuracy adjustment (required calibration weight available on request).**
- **Quantity counting: Reference quantities selectable 1, 5, 10, 20 pieces.**
- **Display selectable between pieces and weight.**
- **Numeric tare preference for well-known container weight. Useful for filling quantities.**
- **Percentage determination: Display of deviation from the reference weight in % instead of in grammes.**
- **KERN Universal Port (KUP): allows the connection of external KUP interface adapters (not included) such as RS-232, USB for exchanging data and control commands, without installation effort.**

Supplied with:

Mains adapter 230 V / 50 Hz and protective hood.

Optional extras:

Internal and external rechargeable battery, calibration weight, wall attachments, printer, stand and interface adapter such as RS-232, USB on request.

Technical description

Settling time	3 s
Reproducibility	0.1 g
Manufacturer's designation	DS
maximum weighing range	0 - 16 kg
Power supply	Mains operated
Scale divisions	0.1 g
Net weight	7.5 kg
Dimensions of weighing plate	308×318 mm
Minimum unit weight	1 g
Calibration	Price on request
Number height display unit	18 mm
Type of product	Platform balance

Services

CalibrationScales maximum weighing range 50 kg	027700 50
--	-----------