




Wire wheel brush Steel wire 0.30 mm, Brush Ø D1× bristle width L1: 125X23mm



Order data

Order number	570120 125X23
GTIN	4067263723783
Item class	57H

Description

Version:

Waved wire firmly crimped into the steel body. **High density**, high concentricity, and good wear resistance. Adaptable to various different mounting bores by use of **interchangeable reducing rings** (supplied).

Application:

Use on bench grinder or polishing machines, or on machines with flexible drive heads. For roughening, cleaning, removing rust, and scale etc.

Technical description

Length of brush section H ₁	27 mm
Brush width	20 mm
maximum speed	6000 min ⁻¹
Bristle thickness	0.35 mm
Reducing ring Ø	12.7 / 16 / 20 / 22.2 / 25.4 / 32 mm

Brush $\varnothing D_1$	125 mm
Bore $\varnothing d_1$	40 mm
Type of product	Wheel brush