


HOLEX**Wire wheel brush Steel wire 0.30 mm, Brush Ø D1× bristle width L1:
100X20mm****Order data**

Order number	570120 100X20
GTIN	4067263723776
Item class	57H

Description**Version:**

Waved wire firmly crimped into the steel body. **High density**, high concentricity, and good wear resistance. Adaptable to various different mounting bores by use of **interchangeable reducing rings** (supplied).

Application:

Use on bench grinder or polishing machines, or on machines with flexible drive heads. For roughening, cleaning, removing rust, and scale etc.

Technical description

Brush width	19 mm
Bristle thickness	0.3 mm
Bore Ø d ₁	30 mm
Length of brush section H ₁	23 mm
maximum speed	8000 min ⁻¹

Reducing ring Ø	12 / 12.7 / 16 / 20 / 22.2 / 25.4 mm
Brush Ø D ₁	100 mm
Type of product	Wheel brush