

HOLEX**Wire wheel brush Brass wire 0.15 mm., Brush Ø D1× bristle width L1:
120X30mm****Order data**

Order number	570170 120X30
GTIN	4067263906506
Item class	57H

Description**Version:**

Waved wire firmly crimped into the steel body. **High density**, high concentricity, and good wear resistance. Adaptable to various different mounting bores by use of **interchangeable reducing rings** (supplied).

Application:

For brass, copper, light alloys, etc. For polishing, fine brushing etc.

Use on bench grinder or polishing machines, or on machines with flexible drive heads.
For roughening, cleaning, removing rust, and scale etc.

Technical description

Bore Ø d ₁	30 mm
Length of brush section H ₁	33 mm
Brush width	25 mm
Reducing ring Ø	12 / 12.7 / 16 / 20 / 22.2 / 25.4 mm

maximum speed	6000 min ⁻¹
Brush Ø D ₁	120 mm
Type of product	Wheel brush