

**HOLEX**

**Wheel brush with shank Brass-coated steel wire 0.25 mm, Brush  $\varnothing$  D1  $\times$  bristle width L1: 70X10mm**



## Order data

Order number	574325 70X10
GTIN	4067263907114
Item class	57H

## Description

### Version:

Waved special high quality wire, **shank  $\varnothing$  6 mm.**

The high-tensile steel wire is coated with a thin layer of brass.

### Application:

For portable grinders, on flexible drive machines or drills for brushing surfaces. High speeds improve the brush performance.

For removal of rust and scale, and for cleaning

## Technical description

Brush $\varnothing$ D <sub>1</sub>	70 mm
Shank $\varnothing$ D <sub>s</sub>	6 mm
Bristle width L <sub>1</sub>	9 mm
maximum speed	15000 min <sup>-1</sup>
Length of brush section H <sub>1</sub>	19 mm

Bristle thickness	0.25 mm
Brush material	Steel wire, brass-coated
Twisted knotting	waved
Type of product	Wheel brush