

**Garant**
**Cleaning disc (A), Disc Ø: 115mm**

**Order data**

Order number	566757 115
GTIN	4067263046875
Item class	51E

**Description**
**Version:**

Grinding wheels with synthetic, nylon fleece evenly impregnated with abrasive grit. Extremely **tough, densely woven, fine non-woven abrasive mesh structure** with high **flexibility** and cutting performance.

**Application:**

For cleaning and deburring **with a fine surface finish**.

With glass fibre backing pad for direct clamping on angle grinders.

**Technical description**

maximum speed	11000 min <sup>-1</sup>
Bore Ø	22.23 mm
recommended speed	5000 - 7000 min <sup>-1</sup>
Disc Ø	115 mm
Degree of hardness	soft
Grit designation	medium
Grinding medium code	A

Iron, sulphur and chlorine constituents	< 0,1 %
Shape description	flat
maximum circumferential speed	60 m/s
Type of product	Rough cleaning non-woven abrasive mesh

## User data

	Suitability	V <sub>c</sub>	ISO code
Alu Mg	suitable		
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
Paint	suitable		
Uni	suitable		
wet maximum	suitable only under restricted conditions		
dry	suitable		