

KERN**Precision scales, type PCB, maximum weighing range: 360g**

Order data

Order number	479511 360
GTIN	4045761243187
Item class	47D

Description

Version:

- **Selectable mains and battery operation. Attention: German version! Please order a GB adapter plug No. 08 1174_GB separately. Auto-off after 3 minutes.**
- **Adjustment programme CAL: For accuracy adjustment (external calibration weight available on request if required).**
- **Quantity counting: Reference quantities selectable 5, 10, 25, 50 pieces. Display selectable between pieces and weight.**
- **Formulation: separate memory for weight of the tare vessel and of the formulation ingredients (net total).**

KERN Universal Port (KUP): allows the connection of external KUP interface adapters, such as RS-232 or USB, for exchanging data and control commands, without installation effort.

Supplied with:

Mains adapter 230 V/ 50 Hz and protective hood.

Optional extras:

Battery No. 081561 size 6LR61; internal rechargeable battery on request. Data cable, printer, interface adapter such as RS-232 or USB on request.

Technical description

Power supply	Battery-powered
--------------	-----------------

Article no of the battery / rechargeable battery fitted	081561 6LR61
Scale divisions	0.001 g
Number of batteries contained	1
Minimum unit weight	0.02 g
Dimensions of weighing plate	Ø 82 mm
Linearity	±0.005 g
maximum weighing range	360 g
Height	79 mm
Net weight	0.84 kg
Reproducibility	0.001 g
Width	163 mm
Depth	245 mm
Settling time	3 s
Calibration	K2
Type of product	Precision balance

Services

DAkkS calibrationScales maximum weighing range 50	027710 50
CalibrationScales maximum weighing range 50 kg	027700 50