


**HOLEX**

**Wheel brush with shank Stainless steel wire 0.30 mm, Brush  $\varnothing$  D1  $\times$  bristle width L1: 50X15mm**



## Order data

Order number	574225 50X15
GTIN	4067263880790
Item class	57H

## Description

### Version:

Waved special high quality wire, **shank  $\varnothing$  6 mm.**

### Application:

For portable grinders, on flexible drive machines or drills for brushing surfaces. High speeds improve the brush performance.

For removal of rust and scale, and for cleaning

## Technical description

Brush $\varnothing$ D <sub>1</sub>	50 mm
maximum speed	15000 min <sup>-1</sup>
Bristle thickness	0.2 mm
Length of brush section H <sub>1</sub>	12 mm
Bristle width L <sub>1</sub>	15 mm
Shank $\varnothing$ D <sub>s</sub>	6 mm

Brush material	Stainless steel wire
Twisted knotting	waved
Type of product	Wheel brush