


HOLEX
Wheel brush with shank Brass wire 0.20 mm., Brush \varnothing D1 \times bristle width L1: 30X6mm

Order data

Order number	574360 30X6
GTIN	4067263934806
Item class	57H

Description
Version:

Waved special high quality wire, **shank \varnothing 6 mm.**

Application:

For portable grinders, on flexible drive machines or drills for brushing surfaces. High speeds improve the brush performance.

For heavy-duty deburring and brushing of non-ferrous metals

Technical description

Brush \varnothing D ₁	30 mm
maximum speed	20000 min ⁻¹
Bristle width L ₁	6 mm
Shank \varnothing D _s	6 mm
Bristle thickness	0.2 mm
Length of brush section H ₁	6 mm

Brush material	Brass wire
Twisted knotting	waved
Type of product	Wheel brush