


Garant
Hydraulic chuck BASIC short, slim, HSK-F 63, Clamping \varnothing D1: 20mm

Order data

Order number	307516 20
GTIN	4067263239758
Item class	31A

Description
Version:

- Axial length adjustment, adjustment travel 10 mm.
- With RFID/Balluffchip bore.

Application:

- High metal removal rate (but not for extreme heavy machining).
- For drilling, reaming and milling.

Optional extras:

Reducing sleeves No. 302135 – 302187, coolant tube No. 309880, socket wrench No. 309890, parallel wipers No. 343720.

Note:

A-dimension = 200 mm available on request!

Technical description

L ₂	48 mm
L ₃	51 mm
Clamping \varnothing D ₁	20 mm
Thread M	M16×1
\varnothing D ₂	42 mm
Adjustment travel V	10 mm

suitable reducing adapter	302155; 302160; 302165; 302150
Overhang dimension A	90 mm
External Ø D	50 mm
Adapter	HSK-F 63
Arbor standard	DIN 69882-7
Arbor standard	DIN 69893
Arbor standard	ISO 12164-1
Shape	F
Through-coolant	yes, with max. 80 bar
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 µm
Machining strategy	HSC
Balluffchip bore	yes
Type of product	Hydraulic chuck

Accessories

Cylindrical cleaner Plastic Pin Ø 20 mm	343720 20
---	-----------