

Garant GRIDLINE

**Support cabinet, for insert size length×width: 1500X1000mm**

**Order data**

|              |                  |
|--------------|------------------|
| Order number | 431060 1500X1000 |
| GTIN         | 4067263264934    |
| Item class   | 41C              |

**Description**
**Version:**

Sturdy welded construction including levelling fittings. Uneven floors can be compensated using height compensation screws.

**Support cabinet**, casing of sheet steel, with swing door (including storage shelf) and / or drawers depending on size, including GARANT locking system. Paint finish of the shell RAL7035 light grey, front faces RAL 7016 anthracite.

**Fitted with:**

Drawer front height (right): 50; 75; 75; 100; 125 mm

Door usable height: 425 mm

Number of shelves: 1

Number of cabinet casings with door: 1

Number of cabinet casings with drawers: 1

**Note:**

For vibration-absorbing machine mounts, please order 4 pcs. No. 086002 size 850.

**Technical description**

|                       |         |
|-----------------------|---------|
| Support cabinet width | 1106 mm |
| Door usable height    | 425 mm  |
| Drawer usable depth   | 500 mm  |

|  |                |
|--|----------------|
| Load capacity, distributed                       | 2000 kg        |
| Support cabinet depth                            | 800 mm         |
| Support cabinet height                           | 710 mm         |
| Height of support cabinet incl. bearing sets     | 770 mm         |
| Drawer usable width                              | 500 mm         |
| Drawer usable width in G                         | 20 mm          |
| Drawer usable depth in G                         | 20 mm          |
| Number of shelves                                | 1 mm           |
| Drawer/pull-out shelf load capacity              | 75 kg          |
| Drawer runner extension (partial/full extension) | 100 %          |
| Height adjustment                                | 25 mm          |
| Hoffmann perforated panel grid interval          | 9×9            |
| Cylinder lock                                    | modular barrel |
| Type of product                                  | Sub-frame      |