

**KÄRCHER****Industrial vacuum cleaner, Manufacturer's designation: IVRL-100DP****Order data**

Order number	078522 IVRL-100DP
GTIN	4054278695136
Item class	07D

**Description****Version:**

Industrial vacuum cleaner suitable for vacuuming up and separating **coolants, lubricating emulsions, water or oil with solids (e.g. metal chips)**.

- **Compact design and robust materials for the best movement characteristics.**
- **Maximum flexibility in use and long working life for the oil-resistant power cable.**
- **Suction is applied via a 360° rotatable hose connection on the suction head.**

2-motor 2.4 kW industrial vacuum cleaner with **tilting mobility trolley, 100 litre tank and integral barrel pump** for easy and complete emptying.

**Supplied with:**

With tilting chassis, and drain hose with level indicator. **Without accessories. Suitable accessories can be found under No. 078524, 078529 and 078533.**

**Note:**

A version with 100-litre stainless steel container can be found under No. 078522 size IVR-L100DP in our eShop.

**Technical description**

Connection width	DN50 mm
------------------	---------

Height	1320 mm
Container volume	100 l
Power consumption	2400 W
Width	660 mm
Vacuum	230 mbar
Weight	57 kg
Number of turbines	2
Operating noise	68 dB(A)
On/Off switch	yes
Power supply	Mains operated
Length	840 mm
Dust class – vacuum cleaner	L
Air flow volume	148 l/s
Cable length	6 m
Type of product	Wet and dry vacuum cleaners