

**Garant**
**Face driver set With morse taper / cylindrical, clockwise operation, Type: 3**

**Order data**

Order number	327455 3
GTIN	4067263557982
Item class	31G

**Description**
**Version:**

- **Constant face driver head with 60° tip angle for use in turning and grinding.**
- **Face driver with spring-loaded, clampable centring point for a backlash-free, stable clamping situation.**
- **High concentricity thanks to fully ground mechanical components.**
- **Perfect in combination with our lathe centres No. 321720, 311750 or 321770.**
- **Conveniently in the GARANT system box 630320.**

**Supplied with:**

- **1 pc. face driver base body No. 327465 (suitable for clockwise and anti-clockwise rotation).**
- **2 pcs. centring point No. 327488.**
- **2 pcs. driver heads No. 327470.**

**Technical description**

Centre tip Ø	4; 6 mm
Working range Ø	9 - 16 mm
Working range Ø	13 - 24 mm
Type of product	Face driver

## Accessories

Face driver With morse taper / cylindrical Type 3	327465 3
Direct toothed driver head, ground Right-hand Working range $\varnothing$ 13-24 mm	327470 13-24
Direct toothed driver head, ground Right-hand Working range $\varnothing$ 9-16 mm	327470 9-16
Centring point for face driver Centring tip $\varnothing$ D 4 mm	327488 4
Centring point for face driver Centring tip $\varnothing$ D 6 mm	327488 6