



## MultiMaster MM 500 Plus Top, Type: 72296770



### Order data

Order number	077814 72296770
GTIN	4014586897813
Item class	03F

### Description

#### Version:

Market-leading oscillating tools in three different performance classes (SuperCut, MultiMaster, MultiTalent) in a new version with **Starlock tool arbor** (improved torque transmission of up to 35 % greater rate of progression of the work).

- **Virtually unlimited application possibilities (sawing, grinding, scraping, cutting, rasping) due to the oscillating mode of movement (low generation of dust).**
- **Stepless electronic speed control for optimum working.**
- **Very high quality and stability thanks to the metal gearbox and use of ball bearings and needle bearings throughout.**
- **Optimum handling due to ergonomic design with soft-grip inlays and low weight.**

Powerful MultiTool for rapid work progress (for interior work and renovation) with more than 30 accessories for sawing wood and metal, cutting tiles, and more.

#### Supplied with:

30-piece accessories set, dust extractor and L-BOXX.

30-piece accessories set consisting of: 1× E-Cut long-life saw blade (10 mm), 2× E-Cut long-life saw blades (35 mm), 2× E-Cut long-life saw blades (65 mm), 1× E-Cut Carbide Pro saw blades (32 mm), 1× carbide saw blade (Ø 75), 1× carbide rasp (three-square), 1× scraper, 1× perforated abrasive plate, 1× each perforated abrasive plate (K60, K80, K120, K180).

### Technical description

Amplitude (oscillation movement)	2 × 1.7 °
----------------------------------	-----------

Speed of oscillation	10000 - 19500 min <sup>-1</sup>
Weight	1.4 kg
Power consumption	350 W
Toolholder	Starlock, Starlock Plus
Power supply	Mains-powered
Manufacturer's designation	MM 500 PLUS TOP
Cable length	5 m
Packaging	Modular case (L-Boxx)
Type of product	Oscillator