

**Garant**
**Face driver With morse taper / cylindrical, Type: 5**

**Order data**

|              |               |
|--------------|---------------|
| Order number | 327465 5      |
| GTIN         | 4067263558149 |
| Item class   | 31G           |

**Description**
**Version:**

Face driver with spring-loaded centring point. The clamping of the centring point when the driver head makes flat surface contact ensures a backlash-free, stable clamping situation. High concentricity thanks to fully ground mechanical components, without centring point and driver heads, suitable for clockwise and anti-clockwise operation. Fully mechanical design with spring force. No leakages from hydraulic fluid. Option for direct clamping on the head on raised collar in soft shaped jaws.

**Suitable for:**

Lathe centres No. 321720, 321750 and 321770.

**Optional extras:**

Driver heads No. 327470 - 327486 and old version No. 327601 – 327651, centring point No. 327488, taper sleeves No. 327492.

**Technical description**

|                        |             |
|------------------------|-------------|
| maximum body Ø         | 75 mm       |
| Weight                 | 3.6 kg      |
| Version                | Morse taper |
| Shank Ø D <sub>s</sub> | 67 mm       |
| Length C               | 197 mm      |

Type of product

Face driver