

mimatic
Tool Systems
Saw blades PolySAW-G Width $a_p = 1.5$ mm, TiAlN, \varnothing D: 63mm


Order data

Order number	218226 63
GTIN	2050001737175
Item class	29C

Description

Version:

For parting off, sawing, and slitting.
 PolySAW-G permits cutting to the full depth.

Note:

Standard application values for a_e max.

Technical description

Type of toolholder	16/26
Engagement depth $a_{e\max}$ per cut	18.5 mm
Insert width E	6 mm
\varnothing D	63 mm
Number of cutting edges Z	24
Shank	with bore
Coating	TiAlN

Feed f_z	0.025 mm
Material	Solid carbide
Type of product	Cutter insert for milling

User data

	Suitability	V_c	ISO code
Alu plastics	suitable	600 m/min	N
Aluminium (short chipping)	suitable	500 m/min	N
Alu > 10% Si	suitable	400 m/min	N
wet maximum	suitable		
dry	suitable only under restricted conditions		

Accessories

ToolholderWeldon shank Type 16/26	218205 16/26
PolySAW toolholderwith bore Type 16/26	218210 16/26