

Garant
Finish milling head, 45° chamfer, HB730, Ø D h10: 12mm

Order data

| | |
|--------------|---------------|
| Order number | 210340 12 |
| GTIN | 4045197523358 |
| Item class | 21M |

Technical description

| | |
|---|---------------------------|
| Head length l | 22 mm |
| Cutter Ø D | 12 mm |
| Flute length L ₂ | 15 mm |
| Corner chamfer width at 45° | 0.24 mm |
| Feed f _z for side milling in steel < 900 N/mm ² | 0.06 mm |
| Arbor size | 12 mm |
| Corner chamfer angle | 45 degrees |
| Number of cutting edges Z | 6 |
| Series | TopCut |
| Grade | HB730 |
| Tool material | Solid carbide |
| Standard | Manufacturer's standard |
| Type | N |
| Helix angle | 50 degrees |
| Direction of infeed | horizontal |
| Cutting width a _e for milling operation | 0.1×D for side milling mm |

| | |
|--------------------|---------------------------|
| Machining strategy | HPC |
| Through-coolant | no |
| suitable arbor | GARANT TopCut |
| Type of product | Cutter insert for milling |

User data

| | Suitability | V _c | ISO code |
|--------------------------------|---|----------------|----------|
| Steel < 500 N/mm ² | suitable | 210 m/min | P |
| Steel < 750 N/mm ² | suitable | 170 m/min | P |
| Steel < 900 N/mm ² | suitable | 150 m/min | P |
| Steel < 1100 N/mm ² | suitable | 130 m/min | P |
| Steel < 1400 N/mm ² | suitable only under restricted conditions | 110 m/min | P |
| Steel < 55 HRC | suitable only under restricted conditions | 50 m/min | H |
| Steel < 60 HRC | suitable only under restricted conditions | 40 m/min | H |
| INOX < 900 N/mm ² | suitable | 80 m/min | M |
| INOX > 900 N/mm ² | suitable only under restricted conditions | 50 m/min | M |
| Ti > 850 N/mm ² | suitable only under restricted conditions | 80 m/min | S |
| GG(G) | suitable | 160 m/min | K |
| Oil | suitable only under restricted conditions | | |
| wet maximum | suitable | | |
| wet minimum | suitable only under restricted conditions | | |
| dry | suitable only under restricted conditions | | |
| Air | suitable | | |

Accessories

| | |
|---|-------------|
| Plug-in adapter for torque wrench Type 10X4 | 219986 10X4 |
| Assembly wrench Type 10X4 | 219987 10X4 |