

Garant
ANGX 10T308ZEER, HB9745, Type: TI

Order data

| | |
|--------------|---------------|
| Order number | GG2134 TI |
| GTIN | 4067263078883 |
| Item class | GGN |

Description
Suitable for:

GARANT Power Q Mini high feed rate indexable milling cutters No. 213052 – 213058.

Content:

50 × 213072 TI

Note:

Standard application values for $a_e = 0.5...1 \times D/a_{p\max}$.

Technical description

| | |
|---------------------------------------|------------|
| Feed f_z per tooth | 0.5 mm |
| Contents | 50 |
| ISO code indexable insert | ANGX10T308 |
| Grade | HB9745 |
| Tool material | Carbide |
| recommended cutting depth $a_{p\max}$ | 0.6 mm |
| maximum cutting depth $a_{p\max}$ | 1 mm |
| Programming radius at $a_{p\max}$ | 1.6 mm |
| Number of changes/inserts | 4 |

Type of product

Indexable insert for milling

User data

| | Suitability | V_c | ISO code |
|----------------------------|---|----------------------|-----------------|
| Ti > 850 N/mm ² | suitable | 50 m/min | S |
| wet maximum | suitable only under restricted conditions | | |
| Air | suitable | | |

Accessories

ANGX 10T308ZEER Type TI

213072 TI