

Mobile lift table, Load capacity: 800kg



Order data

Order number	919989 800
GTIN	4025092253475
Item class	08Y

Description

Version:

Mobile lift table in robust single-scissor construction with solid steel scissors. Swivelling platform with mechanical locking for safe maintenance. Compact chassis with low overall height, swivel and fixed castors made of polyamide with maintenance-free ball bearings, parking brakes on the swivel castors. Manual hydraulics with foot lever. High safety thanks to overload valve and lowering brake valve. Swivel castors \varnothing 150 mm, load castors \varnothing 200 mm. Roller width 50 mm.

Standard:

DIN EN 1570-1; EG-Maschinenrichtlinie 2006/42/EG.

Technical description

Weight	222 kg
Width	860 mm
Material of wheels	Polyamide
Lift range	360 - 1050 mm
Platform area width	840 mm
Platform area length	1350 mm
Load capacity	800 kg

Overall height C	360 mm
Length L	1650 mm
Lift height H	690 mm
Type of product	Lifting table cart