

HOLEX
HOLEX Pro INOX solid carbide high-performance drill, plain shank DIN 6535 HB, AlTiN, Ø DC m7: 8mm

Order data

Order number	GG2491 8
GTIN	4067263087403
Item class	GGN

Description
Version:
Same as No. 122490.

 Efficient drilling especially for use in **stainless and acid-resistant steels.**

 Straight main cutting edges with **optimised cutting edge design** for improved chip breaking behaviour. Enlarged chip grooves for **excellent chip evacuation**. Increased wear resistance due to **improved carbide substrate** and **high temperature resistant coating**.

Note:

 Flute length $L_c = L_2 + 1.5 \times D_c$.

Technical description

Flute length L_c	41 mm
Standard	DIN 6537 K
Feed f in stainless steel < 900 N/mm ²	0.1 mm/rev.
Tolerance nominal Ø	m7
Number of cutting edges Z	2

Nominal $\varnothing D_c$	8 mm
Contents	5
Overall length L	79 mm
recommended maximum drilling depth L_2	29 mm
Shank $\varnothing D_s$	8 mm
Series	Pro Inox
Coating	AlTiN
Tool material	Solid carbide
Version	4xD
Point angle	140 degrees
Shank	DIN 6535 HB to h6
Through-coolant	yes, with 25 bar
Colour ring	blue
Type of product	Twist Drill

User data

	Suitability	V_c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	140 m/min	N
Alu > 10% Si	suitable only under restricted conditions	120 m/min	N
Steel < 500 N/mm ²	suitable	120 m/min	P
Steel < 750 N/mm ²	suitable	110 m/min	P
Steel < 900 N/mm ²	suitable	90 m/min	P
Steel < 1100 N/mm ²	suitable	80 m/min	P
INOX < 900 N/mm ²	suitable	55 m/min	M
INOX > 900 N/mm ²	suitable	45 m/min	M
Ti > 850 N/mm ²	suitable	35 m/min	S
wet maximum	suitable		

wet minimum

suitable only under
restricted conditions

AccessoriesHOLEX Pro INOX solid carbide high-performance drill, plain
shankDIN 6535 HA Ø DC m7 8 mm

122490 8

HOLEX Pro INOX solid carbide high-performance drill, plain
shankDIN 6535 HB Ø DC m7 8 mm

122491 8