

**Garant****Burr GARANT Master Uni – medium, Carbide, Type: E1220****Order data**

Order number	540355 E1220
GTIN	4067263736806
Item class	51D

**Description****Version:**

**GARANT** burrs are manufactured from the highest quality carbide with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide.

**Shank length 200 mm** (can be cut to length).

Shank  $\varnothing$  6 mm.

**Application:**

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Do not start the machine until the burr is inside the component.

**Technical description**

Head $\varnothing$	12 mm
Overall length	220 mm
Head length	20 mm
Shape description	teardrop
Series	GARANT Master Uni
Tool material	Carbide
Type of product	Burr

**User data**

	<b>Suitability</b>	<b>V<sub>c</sub></b>	<b>ISO code</b>
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
INOX	suitable only under restricted conditions		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
Uni	suitable		