



## High-performance heavy-duty side cutter TwinForce®, polished, with grips, overall length: 180mm



### Order data

Order number	723181 180
GTIN	
Item class	73F

### Description

#### Version:

Heavy-duty head, induction hardened cutting edges (approx. 64 HRC), laid-on joint with eccentric double-joint design.

Pliers chemically blacked, head bright polished, handles with multi-component covering and KNIPEXtend interface.

KNIPEXtend is used to connect extensions, such as ColourCode Clips (CCCs) for customisation or TetheredTool Clips (TTCs) for attaching a Tethered Tools fall protection device.

#### Advantage:

**Superior heavy-duty side cutter requiring 50 % less applied force** than conventional heavy-duty side cutters of the same size. Reapplying the tool reduces the force required.

#### Advantage of the advertising text:

**Superior heavy-duty side cutter requiring 50 % less applied force** than conventional heavy-duty side cutters of the same size. Set-back jaws reduce the force required.

#### Standard:

**DIN ISO 5749**

#### Material:

Chrome vanadium steel, drop-forged and oil-hardened.

#### Note:

Previous model No. 723180 can still be ordered until the KNIPEXtend models are available.

### Technical description

Cutting capacity hard wire up to Ø	3.2 mm
Cutting capacity piano wire up to Ø	3 mm

overall length	180 mm
Manufacturer's designation	TwinForce
Cutting capacity soft wire up to Ø	5.5 mm
Standard	DIN ISO 5749
Handle	plastic coated
Manufacturing process	Cutting edges induction hardened (approx. 64 HRC)
Material	Chromium vanadium steel
Surface	Jaws chemically blacked, head bright polished
Heavy-duty diagonal side cutter	yes
with selectable return spring	no
Type of product	Cutting pliers