

## Garant

### Burr set 8 pieces, GARANT Master Alu – very coarse, Carbide, Number of burrs: 8



#### Order data

Order number	547605 8
GTIN	4067263736264
Item class	51D

#### Description

##### Version:

**Multi Cut carbide burr set with popular shape variants.**

The newly developed innovative tooth geometry permits a **high metal removal rate** and at the same time **extremely smooth running and very good guidance**. The optimum chip formation (no pointed chips) achieves high surface quality in roughing and finishing applications.

- **High rate of material removal.**
- **Smooth running.**
- **Low thermal stress, long tool life, improved chip evacuation.**
- **For general-purpose use on steel, stainless steel, aluminium.**

Shank Ø 6 mm.

**GARANT** burrs are manufactured from high performance carbide grades with high wear-resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide.

##### Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning,

weld and surface preparation.

**Supplied with:**

1 pc. each No. 547600 size AS0616; AS1225; C0616; C1225; D0807; F0618; F1225; L1020.

**Note:**

Materials with poor heat conductivity; reduce speed to avoid overheating of the burr and smearing.

## Technical description

Series	GARANT Master Alu
Tool material	Carbide
Shank Ø	6 mm
Number of burrs	8
Type of product	Burr

## Accessories

BurrGARANT Master Alu – very rough (non-ferrous / aluminum) Type AS0616	547600 AS0616
BurrGARANT Master Alu – very rough (non-ferrous / aluminum) Type AS1225	547600 AS1225
BurrGARANT Master Alu – very rough (non-ferrous / aluminum) Type C0616	547600 C0616
BurrGARANT Master Alu – very rough (non-ferrous / aluminum) Type C1225	547600 C1225
BurrGARANT Master Alu – very rough (non-ferrous / aluminum) Type D0807	547600 D0807
BurrGARANT Master Alu – very rough (non-ferrous / aluminum) Type F0618	547600 F0618
BurrGARANT Master Alu – very rough (non-ferrous / aluminum) Type F1225	547600 F1225
BurrGARANT Master Alu – very rough (non-ferrous / aluminum) Type L1020	547600 L1020