


HOLEX**Wire wheel brush Steel wire 0.30 mm, Brush Ø D1× bristle width L1:
250X30mm****Order data**

Order number	570120 250X30
GTIN	4067263723790
Item class	57H

Description**Version:**

Waved wire firmly crimped into the steel body. **High density**, high concentricity, and good wear resistance. Adaptable to various different mounting bores by use of **interchangeable reducing rings** (supplied). Bore with double spline.

Application:

Use on bench grinder or polishing machines, or on machines with flexible drive heads. For roughening, cleaning, removing rust, and scale etc.

Technical description

Brush width	25 mm
Brush Ø D ₁	250 mm
Length of brush section H ₁	50 mm
maximum speed	3600 min ⁻¹
Bore Ø d ₁	50.8 mm

Bore Ø can be opened up to	80 mm
Reducing ring Ø	12/12.7/16/20/22.2/25.4/30 mm
Type of product	Wheel brush