

HOLEX**Deburring wheel brush Steel wire 0.35 mm, Brush Ø D1× bristle width L1:
250X60mm****Order data**

Order number	570505 250X60
GTIN	4067263906551
Item class	57H

Description**Version:**

Bore diameter 50.8 mm with double keyway 13×7. Other bore diameters available.

Waved high-tensile **steel wire**.

Application:

For all popular bench deburring machines. Particularly long working life due to special wire. Ideally suited for economical deburring of flat strips, profiles, pipes, fittings, plastic parts, and the like.

Keyway 13.5×7.6.

Note:

Only the tips of the bristles act on the workpiece. Applying too much contact pressure will not improve the result, but will increase the required drive power and reduce the working life of the brush.

Technical description

maximum speed	3600 min ⁻¹
Brush Ø D ₁	250 mm

Brush width	58 mm
Length of brush section H ₁	50 mm
Brush material	Steel wire
Bristle thickness	0.35 mm
Propulsive equipment	Bench deburrer
Type of product	Wheel brush