


## Garant

**Solid carbide deburrer, spiral flutes 90°, TiSiN, Ø h6 DC: 16mm**



### Order data

Order number	GG8156 16
GTIN	4067263091356
Item class	GGN

### Description

**Version:**

**Same as No. 208156.**

Deburrer for **universal application** on virtually all materials. The newly developed coating effectively prevents built-up edges, even in aluminium or stainless steel.

Tolerance: **Dimension S = +/- 0.2 mm.**

**Point angle = +/- 5 arc minutes.**

**Outstanding surface qualities** thanks to the 35° **helix angle**.

**Application:**

Perfectly suitable for **chamfering** and **deburring** component edges and for **contouring applications**.

### Technical description

Feed $f_z$ in steel < 900 N/mm <sup>2</sup>	0.1 mm
Cutting edge Ø $D_c$	16 mm
Shank Ø $D_s$	16 mm
No. of teeth Z	4
Chamfer mill	45 degrees

Dimension S	11.2 mm
Overall length L	93 mm
Corner chamfer angle	45 degrees
Shank	DIN 6535 HA to h6
Contents	5
Coating	TiSiN
Tool material	Solid carbide
Standard	Works standard
Type	N
Tolerance nominal $\varnothing$	h6
Helix angle	35 degrees
Direction of infeed	horizontal, oblique and vertical
Countersink tip angle	90 degrees
Through-coolant	no
Shank tolerance	h6
Colour ring	green
Type of product	Deburrers

## User data

	Suitability	$V_c$	ISO code
Alu plastics	suitable only under restricted conditions	180 m/min	N
Aluminium (short chipping)	suitable	300 m/min	N
Alu > 10% Si	suitable	220 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	130 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	115 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	110 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	80 m/min	P

Steel < 1400 N/mm <sup>2</sup>	suitable only under restricted conditions	65 m/min	P
Steel < 55 HRC	suitable only under restricted conditions	35 m/min	H
INOX < 900 N/mm <sup>2</sup>	suitable	90 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable	70 m/min	M
Ti > 850 N/mm <sup>2</sup>	suitable	50 m/min	S
GG(G)	suitable	100 m/min	K
Uni	suitable		
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		
dry	suitable only under restricted conditions		
Air	suitable only under restricted conditions		

## Accessories

Solid carbide deburrer, spiral flutes 90° Ø h6 DC 16 mm

208156 16