

HOLEX**Wheel brush Steel wire 0.50 mm, Brush Ø D1× bore Ø d1 / thread M:
125XM14mm****Order data**

Order number	571203 125XM14
GTIN	4067263906582
Item class	57H

Description**Version:**

Straight round brush with smooth wire 0.50 mm, **knotted** and firmly crimped into the steel body. **Very aggressive brushing effect with high wear resistance.**

Application:

For heavy brush work, e.g. descaling, removing rust, removing paint, roughening, cleaning metal parts, also for cleaning formwork boards.

Left knotted, reliably avoids premature unwinding. With **internal thread M14**, for direct mounting **on angle grinders**.

Technical description

maximum speed	12500 min ⁻¹
Bristle width L ₁	14 mm
Bristle thickness	0.5 mm
Number of twisted knots	20

Thread M	M14
Brush \varnothing D ₁	125 mm
Length of brush section H ₁	29 mm
Brush material	Steel wire
Type of product	Wheel brush