

**HOLEX****Wheel brush Steel wire 0.50 mm, Brush Ø D1× bore Ø d1 / thread M:  
115XM14mm****Order data**

Order number	571203 115XM14
GTIN	4067263906568
Item class	57H

**Description****Version:**

Straight round brush with smooth wire 0.50 mm, **knotted** and firmly crimped into the steel body. **Very aggressive brushing effect with high wear resistance.**

**Application:**

For heavy brush work, e.g. descaling, removing rust, removing paint, roughening, cleaning metal parts, also for cleaning formwork boards.

**Left knotted**, reliably avoids premature unwinding. With **internal thread M14**, for direct mounting **on angle grinders**.

**Technical description**

Bristle thickness	0.5 mm
Length of brush section H <sub>1</sub>	24 mm
Brush Ø D <sub>1</sub>	115 mm
Number of twisted knots	20

maximum speed	12500 min <sup>-1</sup>
Thread M	M14
Bristle width L <sub>1</sub>	14 mm
Brush material	Steel wire
Type of product	Wheel brush