

HOLEX**Wheel brush with shank Steel wire 0.30 mm, Brush Ø D1× bristle width L1:
70X16mm****Order data**

Order number	574050 70X16
GTIN	4067263907022
Item class	57H

Description**Version:**

Waved special high quality wire, **shank Ø 6 mm.**

Application:

For portable grinders, on flexible drive machines or drills for brushing surfaces. High speeds improve the brush performance.

For removal of rust and scale, and for cleaning

Technical description

Shank Ø D _s	6 mm
Length of brush section H ₁	19 mm
Bristle thickness	0.3 mm
Bristle width L ₁	14 mm
Brush Ø D ₁	70 mm
maximum speed	15000 min ⁻¹

Brush material	Steel wire
Twisted knotting	waved
Type of product	Wheel brush