


HOLEX
Wheel brush with shank Steel wire 0.20 mm, Brush Ø D1× bristle width L1: 50X15mm

Order data

Order number	574150 50X15
GTIN	4067263907060
Item class	57H

Description
Version:

Waved special high quality wire, **shank Ø 6 mm.**

Application:

For portable grinders, on flexible drive machines or drills for brushing surfaces. High speeds improve the brush performance.

For removal of rust and scale, and for cleaning

Technical description

maximum speed	15000 min ⁻¹
Brush Ø D ₁	50 mm
Shank Ø D _s	6 mm
Bristle thickness	0.2 mm
Bristle width L ₁	15 mm
Length of brush section H ₁	12 mm

Brush material	Steel wire
Twisted knotting	waved
Type of product	Wheel brush