



## Wheel brush with shank Brass-coated steel wire 0.25 mm, Brush $\varnothing$ D1 $\times$ bristle width L1: 50X10mm



### Order data

Order number	574325 50X10
GTIN	4067263907107
Item class	57H

### Description

#### Version:

Waved special high quality wire, **shank  $\varnothing$  6 mm.**

The high-tensile steel wire is coated with a thin layer of brass.

#### Application:

For portable grinders, on flexible drive machines or drills for brushing surfaces. High speeds improve the brush performance.

For removal of rust and scale, and for cleaning

### Technical description

maximum speed	15000 min <sup>-1</sup>
Bristle thickness	0.25 mm
Bristle width L <sub>1</sub>	10 mm
Shank $\varnothing$ D <sub>s</sub>	6 mm
Brush $\varnothing$ D <sub>1</sub>	50 mm

Length of brush section H <sub>1</sub>	12 mm
Brush material	Steel wire, brass-coated
Twisted knotting	waved
Type of product	Wheel brush